


coding style table

	style A: for connectors 6-pole
	style B: for connectors from 10 to 14-pole
	style C: for connectors from 16 to 64-pole

further information see: DS 09182100600

	All rights reserved Department EC PD - DE	Created by STORCK	Inspected by LEHNERT	Standardisation HOFFMANN	Date 2016-04-05	State Final Release	Ref. Sub.
	HARTING Electronics GmbH D-32339 Espelkamp	Title SEK 18 female conn with closed end cover strain relief			Doc-Key / ECM-Nr. 100662934/UGD/009/A 50000099698		Rev. A
		Type TB	Number 09185XXX814				

no. of contacts	performance level			insulator colour	dimensions				
	PL3	PL2	S4		A max.	B	C	D	
06	09 18 506 7814	09 18 506 6814	09 18 506 5814	grey	12,2	2 x 2,54 (=5,08)	2	8,02	
10	09 18 510 7814	09 18 510 6814	09 18 510 5814		17,3	4 x 2,54 (=10,16)	3,8	13,1	
14	09 18 514 7814	09 18 514 6814	09 18 514 5814		22,4	6 x 2,54 (=15,24)	3,8	18,18	
16	09 18 516 7814	09 18 516 6814	09 18 516 5814		24,9	7 x 2,54 (=17,78)	3,8	20,72	
20	09 18 520 7814	09 18 520 6814	09 18 520 5814		30	9 x 2,54 (=22,86)	3,8	25,8	
26	09 18 526 7814	09 18 526 6814	09 18 526 5814		37,6	12 x 2,54 (=30,48)	3,8	33,42	
30	09 18 530 7814	09 18 530 6814	09 18 530 5814		42,7	14 x 2,54 (=35,56)	3,8	38,56	
34	09 18 534 7814	09 18 534 6814	09 18 534 5814		47,8	16 x 2,54 (=40,64)	3,8	43,58	
40	09 18 540 7814	09 18 540 6814	09 18 540 5814		55,4	19 x 2,54 (=48,26)	3,8	51,2	
50	09 18 550 7814	09 18 550 6814	09 18 550 5814		68,1	24 x 2,54 (=60,96)	3,8	63,9	
60	09 18 560 7814	09 18 560 6814	09 18 560 5814		80,8	29 x 2,54 (=73,66)	3,8	76,6	
64	09 18 564 7814	09 18 564 6814	09 18 564 5814		85,9	31 x 2,54 (=78,74)	3,8	81,68	
06	09 18 506 7814 001	09 18 506 6814 001	09 18 506 5814 001		black	12,2	2 x 2,54 (=5,08)	2	8,02
10	09 18 510 7814 001	09 18 510 6814 001	09 18 510 5814 001			17,3	4 x 2,54 (=10,16)	3,8	13,1
14	09 18 514 7814 001	09 18 514 6814 001	09 18 514 5814 001	22,4		6 x 2,54 (=15,24)	3,8	18,18	
16	09 18 516 7814 001	09 18 516 6814 001	09 18 516 5814 001	24,9		7 x 2,54 (=17,78)	3,8	20,72	
20	09 18 520 7814 001	09 18 520 6814 001	09 18 520 5814 001	30		9 x 2,54 (=22,86)	3,8	25,8	
26	09 18 526 7814 001	09 18 526 6814 001	09 18 526 5814 001	37,6		12 x 2,54 (=30,48)	3,8	33,42	
30	09 18 530 7814 001	09 18 530 6814 001	09 18 530 5814 001	42,7		14 x 2,54 (=35,56)	3,8	38,56	
34	09 18 534 7814 001	09 18 534 6814 001	09 18 534 5814 001	47,8		16 x 2,54 (=40,64)	3,8	43,58	
40	09 18 540 7814 001	09 18 540 6814 001	09 18 540 5814 001	55,4		19 x 2,54 (=48,26)	3,8	51,2	
50	09 18 550 7814 001	09 18 550 6814 001	09 18 550 5814 001	68,1		24 x 2,54 (=60,96)	3,8	63,9	
60	09 18 560 7814 001	09 18 560 6814 001	09 18 560 5814 001	80,8		29 x 2,54 (=73,66)	3,8	76,6	
64	09 18 564 7814 001	09 18 564 6814 001	09 18 564 5814 001	85,9		31 x 2,54 (=78,74)	3,8	81,68	

	All rights reserved	Created by	Inspected by	Standardisation	Date	State	
	Department EC PD - DE	STORCK	LEHNERT	HOFFMANN	2016-04-05	Final Release	
HARTING Electronics GmbH D-32339 Espelkamp		Title SEK 18 female conn with closed end cover strain relief				Doc-Key / ECM-Nr. 100662934/UGD/009/A 50000099698	
		Type	Number		Rev.	Page	
		TB	09185XXX814		A	2/2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[09185106814](#) [09185107814](#) [09185167814](#) [09185205814](#) [09185206814](#) [09185267814](#) [09185345814](#)
[09185346814](#) [09185347814](#) [09185405814](#) [09185406814](#) [09185407814](#) [09185606814](#) [09185645814](#) [09185067814](#)
[09185207814](#) [09185066814](#) [09185266814](#) [09185506814](#) [09185605814](#) [09185105814](#) [09185146814](#)
[09185505814](#) [09185507814](#) [09185646814](#) [09185147814](#) [09185166814](#) [09185607814](#) [09185647814](#) [09185065814](#)