

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0587210010**
Status: **Active**
Overview: HMC Heavy Duty Rectangular Connectors
Description: HMC Rectangular Industrial Hood Bracket, Multi-Module Type, 48-72 Circuits, Type A Polarization

Documents:

3D Model	Product Specification PS-58719-005-001 (PDF)
Drawing (PDF)	Product Specification PS-58719-006-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	I/O Connectors
Series	58721
Application	Panel-Mount
Component Type	Hood Bracket
Overview	HMC Heavy Duty Rectangular Connectors
Product Name	HMC
Type	N/A
UPC	800753921023

Physical

Circuits (Loaded)	48
Circuits (maximum)	48
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Net Weight	46221.300/mg
Orientation	Vertical
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	N/A
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP65


Electrical

Current - Maximum per Contact	12.0A, 20.0A
Voltage - Maximum	250V AC

Material Info

Reference - Drawing Numbers

Product Specification	PS-58719-005-001, PS-58719-006-001
Sales Drawing	SD-58721-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(b)-II

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[58721 Series](#)

Mates With

[587190010 Panel Mount Bracket](#)

Use With

[51194 Housing](#), [51195 Housing](#),
[58723-0010 Hood](#), [51203 Housing](#), [51204 Housing](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[58721-0010](#)