## Product data sheet Characteristics

# ZCMD21L2

limit switch body ZCMD - 1NC+1NO - silver - snap action - connection - 2 m





#### Main

| Range of product              | OsiSense XC   |
|-------------------------------|---|
| Series name                   | Standard format   |
| Product or component type     | Limit switch body   |
| Device short name             | ZCMD  |
| Design                        | Miniature   |
| Body type                     | Fixed   |
| Associated head               | ZCE10 ZCEF2 ZCE06 ZCE07 ZCE27 ZCE63 ZCE14 ZCEF0 ZCE11 ZCE28 ZCE67 ZCE21 ZCE08 ZCE64 ZCE65 ZCE29 ZCE01 ZCE02 ZCE01 ZCE62 ZCE01 ZCE62 ZCE01 ZCE62 ZCE02 ZCE02 ZCE02 ZCE02 ZCE01 ZCE09 |
| Body material                 | Zamak   |
| Number of poles               | 2   |
| Contacts type and composition | 1 NC + 1 NO   |
| Contact operation             | Snap action   |
|                               |   |

### Complementary

| XCMD   |
|--|
| Removable cable  |
| 6.56 ft (2 m)  |
| 5 x 0.75 mm²   |
| PvR  |
| Zb   |
| Silver plated contacts   |
| With   |
| 0.01 m/min   |
| 300 V 3)UL 508<br>400 V 3)IEC 60947-5-1<br>300 V 3)CSA C22.2 No 14 |
| 25 mOhm conforming to IEC 60255-7 category 3                       |
| 4 KV IEC 60664<br>4 kV IEC 60947-1                                 |
| 6 A cartridge fuse gG  |
|  |

| Electrical durability                          | 5000000 Cycles, DC-13 120 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 24 V, 4 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C   |
|--|---|
| Maximum Width                                  | 1.18 in (30 mm)   |
| Height   | 1.97 in (50 mm)   |
| Depth  | 0.63 in (16 mm)   |
| Net Weight                                     | 0.14 lb(US) (0.065 kg)  |
| Environment                                    |   |
| Ambient air temperature for storage            | -40158 °F (-4070 °C)  |
| Ordering and shipping details                  |   |
| Category                                       | 22413 - LIMIT SWITCH, IEC, MINIATURE  |
| Discount Schedule                              | Т   |
| GTIN   | 00785901660255  |
| Nbr. of units in pkg.                          | 1   |
| Package weight(Lbs)                            | 0.51 lb(US) (0.23 kg)   |
| Returnability                                  | Yes   |
| Country of origin                              | ID  |
| Packing Units Package 1 Height Package 1 width | 0.200 dm<br>1.500 dm  |
| Package 1 Length                               | 1.500 dm  |
| Offer Sustainability                           |   |
| Sustainable offer status                       | Green Premium product   |
| California proposition 65                      | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACh Regulation                               | REACh Declaration   |
| EU RoHS Directive                              | Pro-active compliance (Product out of EU RoHS legal scope) EVEL RoHS Declaration  |
| Toxic heavy metal free                         | Yes   |
| Mercury free                                   | Yes   |
| RoHS exemption information                     | ∰Yes  |
| Environmental Disclosure                       | Product Environmental Profile   |
| Circularity Profile                            | End Of Life Information   |

#### Contractual warranty

| Contraction Warranty |           |
|----------------------|-----------|
| Warranty             | 18 months |