




Pushing Performance

## Han D M Crimpkontakt 1,0 mm<sup>2</sup> GT/SMC



Part number	09 15 000 6302
Specification	Han D M Crimpkontakt 1,0 mm <sup>2</sup> GT/SMC
HARTING eCatalogue	<a href="https://b2b.harting.com/09150006302">https://b2b.harting.com/09150006302</a>

### Identification

Category	Contacts
Series	Han D <sup>®</sup>
Type of contact	Crimp contact

### Version

Gender	Male
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	1 mm <sup>2</sup>
Conductor cross-section	AWG 18
Operating current	≤10 A
Contact resistance	≤3 mΩ
Stripping length	8 mm

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Han <sup>®</sup> -GoldTec
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

## Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

## Commercial data

Packaging size	100
Net weight	0.62 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09150006302](#)