








Transformers



Dimensions (In.)

■ DIMENSIONS AND PERMISSIBLE RIPPLE CURRENT

- Type: shielded audio
- Core size: EI-14
- Impedance: $\pm 10\%$ @ 1KHz
- D.C. resistance: $\pm 15\%$
- Breakdown voltage: 100VAC hipot for 1 minute
- Insulation: $>10M\Omega$ @ 100VDC
- Maximum output: 75mW
- Soldering temperature: 230°C~270°C
- Frequency response: $\pm 2dB$, 300Hz~3.5KHz
- RoHS Compliant

Mouser Stock No.	Impedance Ω		Resistance Ω	
	Pri.	Sec.	Pri.	Sec.
429-7201-RC	500	8	35	1
429-7202-RC	10K	2K	580	200
429-7209-RC	500	500	40	38
429-7216-RC	600	600	65	55
429-7218-RC	7K	10K	400	385



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

[429-7218-RC](#) [429-7209-RC](#) [429-7216-RC](#) [429-7202-RC](#) [429-7201-RC](#)