


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBERS	LEGEND [ each ]	MARKERS PER WAND	MARKERS PER PKG.	STD. PKG. QTY.	STD. CTN. QTY.	WIRE SIZE RANGE
PCA23-A THRU PCA23-Z	'A' THRU 'Z' [ 1 EA. ]	20	60	1	10	.23" - .37"
PCA23-A-D	'A' - 'D' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-E-H	'E' - 'H' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-I-L	'I' - 'L' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-M-P	'M' - 'P' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-Q-T	'Q' - 'T' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-U-X	'U' - 'X' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-Y-Z	'Y', 'Z', '-', '+' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-0 THRU PCA23-9	'0' THRU '9' [ 1 EA. ]	20	60	1	10	.23" - .37"
PCA23-0-3	'0' - '3' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-4-7	'4' - '7' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-8-9	'8', '9', '+', '-' [ 1 EA. ]	20	80	1	10	.23" - .37"
PCA23-MIN	'-'	20	60	1	10	.23" - .37"
PCA23-PLS	'+'	20	60	1	10	.234" - .367"



- NOTES:
- COLOR: WHITE WITH BLACK LEGENDS.
  - MILLIMETERS ARE IN [ ].
  - ONE SIDE PRINTED.

5

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	10/27/15	RVU	SEWH	JHAC	ADD NOTE 3 TO SHOW ONE SIDE PRINTED.	GAECN03229
4	4/22/13	RVU	SEWH	JHAC	CHANGE OLD DRAWING BOARDER TO NEW PANDUIT DRAWING BOARDER.	GAECN02988
3	3/28/11	RVU			UPDATE ON TABLE, NOTES, & TOLERANCES. CHG. FROM B TO A FORMAT. UPDATE TABLE.	6336
2	8/11/10	RVU			ADDED TOLERANCES AND NOTE 1 THRU 5. ADDED PART NUMBERS.	6079
1	10/6/06	RVU			ADDED TOLERANCE AND REVISED TABLE.	4716
0	9/12/06	RVU			DRAWING RELEASE.	4677

TITLE <b>PCA23-* CLIP-ON WIRE MARKER</b>		CUSTOMER DRAWING	
ITEM REVISION NAME 100281DD/06		<b>PANDUIT</b>	
DATASET FILE NAME 100281DD_DC_C10514/06F			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL: <b>WHITE MARKER-ACETAL</b>	
.x ± .12 [ 3.05 ] .xxx ± .025 [ .635 ] .xx ± .062 [ 1.57 ] ANGLES ±		DRAWING NUMBER: C10514	
THIRD ANGLE PROJECTION			
DRAWN BY RVU	DATE 9/12/06	CHK JM	SCALE NTS
SHT 1 OF 1		A	

D10100DA/15

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[PCA23-1](#) [PCA23-7](#) [PCA23-G](#) [PCA23-0-3](#) [PCA23-5](#) [PCA23-0](#) [PCA23-2](#) [PCA23-M](#) [PCA23-Y](#) [PCA23-6](#) [PCA23-V](#)  
[PCA23-J](#) [PCA23-E-H](#) [PCA23-Q-T](#) [PCA23-T](#) [PCA23-8-9](#) [PCA23-W](#) [PCA23-C](#) [PCA23-D](#) [PCA23-H](#) [PCA23-U](#)  
[PCA23-I](#) [PCA23-A-D](#) [PCA23-R](#) [PCA23-N](#) [PCA23-S](#) [PCA23-3](#) [PCA23-M-P](#) [PCA23-A](#) [PCA23-4](#) [PCA23-P](#) [PCA23-](#)  
[X](#) [PCA23-K](#) [PCA23-MIN](#) [PCA23-L](#) [PCA23-F](#) [PCA23-9](#) [PCA23-4-7](#) [PCA23-Q](#) [PCA23-B](#) [PCA23-8](#) [PCA23-O](#)  
[PCA23-Z](#) [PCA23-I-L](#) [PCA23-PLS](#) [PCA23-E](#) [PCA23-Y-Z](#) [PCA23-U-X](#)