

MS3180 and MS3181 Protective Plug and Receptacle Covers

MATING CONNECTOR
MIL-DTL-26482

Attachment Option
C = Chain
N = Chain with Ring (MS3181 Only)
R = Wire Rope

Length
L = Chain or Rope Length of 5 Inches (127.0 mm). Omit for Standard (See K in Table I)

Prior Revision D Available:

Finish is Cadmium Olive Drab

Attachment Option (Omit for None)
C = Chain
N = Chain with Ring (MS3181 Only)

MS3180 - 12 C

Basic Part Number
MS3180 = Plug Cover
MS3181 = Receptacle Cover

Shell Size

NOTE: prior revision parts will NOT carry the "JAN" marking

MS3180 - 12 C A L

Basic Part Number
MS3180 = Plug Cover
MS3181 = Receptacle Cover

Shell Size (Table I)

Finish
A = Anodize






TABLE I: Shell Size, Dimensions and Attachment

Shell Size	F Max	G Dia Max	H Dia Max	J Max	K Standard Length (Inches)	L Min
8	.562 (14.3)	.719 (18.3)	.734 (18.6)	.562 (14.3)	3.00 (76.2)	.578 (14.7)
10	.562 (14.3)	.844 (21.4)	.859 (21.8)	.562 (14.3)	3.00 (76.2)	.703 (17.9)
12	.562 (14.3)	1.000 (25.4)	1.000 (25.4)	.562 (14.3)	3.50 (88.9)	.891 (22.6)
14	.562 (14.3)	1.125 (28.6)	1.125 (28.6)	.562 (14.3)	3.50 (88.9)	1.016 (25.8)
16	.562 (14.3)	1.250 (31.8)	1.250 (31.8)	.562 (14.3)	3.50 (88.9)	1.141 (29.0)
18	.562 (14.3)	1.375 (34.9)	1.375 (34.9)	.562 (14.3)	3.50 (88.9)	1.266 (32.2)
20	.625 (15.9)	1.500 (38.1)	1.500 (38.1)	.562 (14.3)	4.00 (101.6)	1.391 (35.3)
22	.625 (15.9)	1.625 (41.3)	1.625 (41.3)	.562 (14.3)	4.00 (101.6)	1.516 (38.5)
24	.658 (16.7)	1.750 (44.5)	1.750 (44.5)	.602 (15.3)	4.00 (101.6)	1.641 (41.7)

APPLICATION NOTES

1. Assembly identified with manufacturer's name and part number, space permitting.
2. For complete dimensions, see the applicable Military Specification.
3. Metric dimensions (mm) are in parentheses.

Dimensions in inches (millimeters) and are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[MS3180-10CAL](#) [MS3180-12CAL](#) [MS3180-12RAL](#) [MS3180-14CA](#) [MS3180-14CAL](#) [MS3180-14RA](#) [MS3180-16C](#)
[MS3180-16CA](#) [MS3180-16CAL](#) [MS3180-18CA](#) [MS3180-20CA](#) [MS3180-20CAL](#) [MS3180-22CA](#) [MS3180-22CAL](#)
[MS3180-24CAL](#) [MS3180-8CA](#) [MS3180-8CAL](#) [MS3180-8RAL](#) [MS3181-10C](#) [MS3181-10CAL](#) [MS3181-10N](#) [MS3181-](#)
[10RA](#) [MS3181-12CAL](#) [MS3181-12NA](#) [MS3181-12RAL](#) [MS3181-14C](#) [MS3181-14CA](#) [MS3181-14CAL](#) [MS3181-14N](#)
[MS3181-14NA](#) [MS3181-14RA](#) [MS3181-16CA](#) [MS3181-18CA](#) [MS3181-20CA](#) [MS3181-20CAL](#) [MS3181-20NA](#)
[MS3181-22CA](#) [MS3181-22CAL](#) [MS3181-22NA](#) [MS3181-24CA](#) [MS3181-24CAL](#) [MS3181-8CA](#) [MS3181-8N](#) [MS3181-](#)
[8RA](#) [MS3181-16RA](#) [MS3181-8](#) [MS3180-14RAL](#) [MS3180-18CAL](#) [MS3180-22RAL](#) [MS3180-24CA](#) [MS3181-10RAL](#)
[MS3181-12N](#) [MS3181-16N](#) [MS3181-20C](#) [MS3181-24NA](#) [MS3181-8C](#) [MS3181-12C](#) [MS3181-12CA](#) [MS3181-12NAL](#)
[MS3180-12CA](#) [MS3181-10CA](#) [MS3181-10NA](#) [MS3181-16NA](#) [MS3181-8NA](#) [MS3181-18NA](#) [MS3180-10CA](#)
[MS3180-12RA](#) [MS3180-10C](#) [MS3181-22C](#) [MS3180-12C](#) [MS3180-14C](#) [MS3180-18C](#) [MS3181-18C](#) [MS3181-16C](#)
[MS3180-20C](#) [MS3181-20](#) [MS3181-18CAL](#) [MS3181-8CAL](#) [MS3181-8NAL](#) [MS3180-8C](#) [MS3181-18RA](#) [MS3181-24C](#)
[MS3181-12RA](#) [MS3181-16RAL](#) [MS3181-18N](#) [MS3180-16RAL](#) [MS3180-18RA](#) [MS3181-14](#) [MS3181-16CAL](#)
[MS3181-20RAL](#) [MS3181-22RA](#) [MS3180-20RA](#) [MS3180-24](#) [MS3180-18RAL](#) [MS3181-16NAL](#) [MS3181-22NAL](#)
[MS3181-24NAL](#) [MS3181-24N](#) [MS3180-22C](#) [MS3180-16](#)