

M85528/1 Mounting Flange, Full Perimeter

M85528/1-10 A

Basic Part No. _____ A = Primer Coat
Shell Size _____ Required

Note: part superceded by M85049/94




TABLE I

Shell Size	Thread UNJC-3B	A		B		C		D	
		±.003 (.1)	(mm)	±.015 (.4)	(mm)	-.010 (.3)	(mm)	±.030 (.8)	(mm)
8	4-40	.594	(15.1)	.880	(22.4)	.570	(14.5)	.136	(3.5)
10	4-40	.719	(18.3)	1.005	(25.5)	.700	(17.8)	.136	(3.5)
12	4-40	.812	(20.6)	1.098	(27.9)	.820	(20.8)	.136	(3.5)
14	4-40	.906	(23.0)	1.192	(30.3)	.945	(24.0)	.136	(3.5)
16	4-40	.969	(24.6)	1.255	(31.9)	1.070	(27.2)	.136	(3.5)
18	4-40	1.062	(27.0)	1.348	(34.2)	1.196	(30.4)	.136	(3.5)
20	4-40	1.156	(29.4)	1.500	(38.1)	1.320	(33.5)	.136	(3.5)
22	4-40	1.250	(31.8)	1.625	(41.3)	1.440	(36.6)	.136	(3.5)
24	6-32	1.375	(34.9)	1.750	(44.5)	1.570	(39.9)	.153	(3.9)
25	6-32	1.500	(38.1)	1.891	(48.0)	1.658	(42.1)	.153	(3.9)

1. For complete dimensions see applicable Military Specification.
2. Metric dimensions (mm) are indicated in parentheses.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[M85528/1-14A](#) [M85528/1-18A](#) [M85528/1-14](#) [M85528/1-16](#) [M85528/1-18](#) [M85528/1-20](#) [M85528/1-22](#) [M85528/1-24](#)
[M85528/1-25](#) [M85528/1-22A](#) [M85528/1-24A](#) [M85528/1-25A](#) [M85528/1-10](#) [M85528/1-10A](#) [M85528/1-16A](#)
[M85528/1-8](#) [M85528/1-12](#) [M85528/1-12A](#) [M85528/1-20A](#) [M85528/18A](#)