


# Soft face hammers

## 216 Dead-blow hammers, monobloc

- Steel-ball dead-blow design.
- Polyurethane encapsulated steel body and handle.
- Shore hardness D63 on striking faces.
- Ergonomic PVC grip.

➤	Ø	L	l	ΔΔ
	mm	mm	mm	kg
<b>216.40</b>	40	298	110	0,72
<b>216.50</b>	50	308	115	0,95
<b>216.60</b>	60	315	120	1,4



## 212A Dead-blow hammers, interchangeable tips

- Glass-fibre handle.
- Steel body.
- Easily replaceable, special nylon tips. Shore hardness D74.
- Ergonomic ribbed PVC grip.
- Stove-enamel hammer finish.

➤	L	l	Ø	Bits	ΔΔ
	mm	mm	mm		kg
<b>212A.35</b>	305	112	35	212.E35	0,69
<b>212A.40</b>	310	117	40	212.E40	0,76
<b>212A.50</b>	320	120	50	212.E50	1,07
<b>212A.60</b>	330	138	60	212.E60	1,68



## ► Interchangeable-tip mallets

### 207A - 208A Adaptable-tip mallets

207A : Lightweight-series, aluminium body.

208A : Heavyweight-series, brass body.

- Mallets are available with a limited number of tip combinations only, but you can customize your mallet by selecting a body and two tips of your choice.

➤	Lightweight/Heavyweight	Ø	Bits	ΔΔ
		mm		kg
<b>207A.25CB</b>	Lightweight-series	25	EC - EB	0,135
<b>207A.32CB</b>	Lightweight-series	32	EC - EB	0,205
<b>207A.40CB</b>	Lightweight-series	40	EC - EB	0,350
<b>207A.50CB</b>	Lightweight-series	50	EC - EB	0,350
<b>207A.60CB</b>	Lightweight-series	60	EC - EB	0,528
<b>208A.25CB</b>	Heavyweight-series	25	EC - EB	0,220
<b>208A.32CB</b>	Heavyweight-series	32	EC - EB	0,345
<b>208A.32AB</b>	Heavyweight-series	32	EA - EB	0,390
<b>208A.32BB</b>	Heavyweight-series	32	EB - EB	0,375
<b>208A.40CB</b>	Heavyweight-series	40	EC - EB	0,615
<b>208A.40CC</b>	Heavyweight-series	40	EC - EC	0,626
<b>208A.50CB</b>	Heavyweight-series	50	EC - EB	1,050
<b>208A.60CB</b>	Heavyweight-series	60	EC - EB	1,663



### 207A - 208A Mallet bodies

207A : Lightweight aluminium body, hickory handle.

208A : Heavyweight brass body, hickory handle.

➤	Lightweight/Heavyweight	Length	Ø	Hickory	ΔΔ
		mm	mm		kg
<b>207A.25</b>	Lightweight-series	280	25	210.MH12	0,135
<b>207A.32</b>	Lightweight-series	300	32	210.MH13	0,195
<b>207A.40</b>	Lightweight-series	323	40	210.MH14	0,270
<b>207A.50</b>	Lightweight-series	350	50	210.MH15	0,410
<b>207A.60</b>	Lightweight-series	363	60	210.MH16	0,610
<b>208A.25</b>	Heavyweight-series	280	25	210.MH12	0,235
<b>208A.32</b>	Heavyweight-series	300	32	210.MH13	0,340
<b>208A.40</b>	Heavyweight-series	323	40	210.MH14	0,525
<b>208A.50</b>	Heavyweight-series	350	50	210.MH15	0,830
<b>208A.60</b>	Heavyweight-series	363	60	210.MH16	1,260

