


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT CT-1570 TOOL:

TOOL WEIGHT: 26.4 oz. [0.75] kg

Crimps most Panduit #22 - #10 AWG and 0.5 – 6.0 mm² non-insulated terminals, disconnects; and specific non-insulated splices.

Provides UL Listed and CSA Certified terminations with applicable Panduit terminals.

DIMENSIONS SHOWN IN BRACKETS [] ARE METRIC, AND ARE FOR REFERENCE ONLY.

CRIMP POCKET AWG / mm ²	ENGLISH GO / NO GO GAGE MEMBERS		METRIC GO / NO GO GAGE MEMBERS	
	"G" Dia. (GO)	"NG" Dia. (NO GO)	"G" Dia. (GO)	"NG" Dia. (NO GO)
22-18/0,5-1,5	.050"	.063"	1,27mm	1,60mm
16-14/1,5-2,5	.072"	.085"	1,83mm	2,16mm
12-10/4,0-6,0	.097"	.110"	2,46mm	2,79mm

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY:	DATE:	CHK	SCALE	SHT 1 OF 1	SIZE
							BLR	5-11-15	BJPU	NONE		B
01	11-15-16	BLR	BJPU	JADE	UPD TOOL GRAPHIC/BRANDING	10978						
00	5-11-15	BLR	BJPU	ABJ	RELEASED	4857						
---	-----	---	---	---	ADD GO NO GO CHART	-----						

**CT-1570 Contour Crimp™
Crimping Tool**
CUSTOMER DRAWING

ITEM REVISION NAME:
TP27604B01_01

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.x) ± --- (.xxx) ± ---
(.xx) ± --- ANGLES ± ---

THIRD ANGLE
PROJECTION

DRAWING NUMBER:
TP27604B01

MATERIAL:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[CT-1570](#)