

15

KLS 13

Jack connectors





Jack plug acc. to JIS C 6560 JC25P3, 2.5 mm, 3 poles/
stereo, straight version, with bend protection and solder
terminal

State: Active

15

KLS 13



Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body POM
Contact CuZn, nickel-plated
Housing PE

Connectable conductors for solder area

Cable diameter 4 mm

Electrical data (at T_{amb} 20 °C)

Rated current 0,5 A
Rated voltage 34 V AC/DC
Rated impulse voltage 500 V/60 s
Insulation resistance ≥ 100 MΩ

Associated products

Counterparts

☞ 1501 02	☞ 1501 03	☞ 1501 04
☞ 1501 05	☞ 1501 06	☞ 1501 07
☞ 1501 08	☞ KLB 13	

15

KLS 13

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
KLS 13	3	100	500

Packaging:

in bulk, in a cardboard box or a plastic bag