



NEW


Vegas A24

Vibrantly Stylish with aRGB - 240mm

Easily add unique and stylish personalisation to your system with the white Vegas A-series aRGB fans. Available as a single fan, duo or trio of fans that are integrated into one single fan frame design for convenient and quick installation.

Product Code: AK-FN112-WH



Where to Buy 



Application PC case, radiator, heatsink fan

Dimension 245 x 125 x 25 mm

Bearing Two Ball Bearing

Speed 900 - 2000 RPM

Max Airflow 109.48 CFM

Max Static Pressure 2.48 mm-H₂O

Sound Level 19.5 - 37.5 dB(A)

Rated Voltage for Fan 12V DC

Rated Current for Fan 0.25 A (For a single fan)

Voltage Rating for LED 5V DC

Current Rating for LED 0.5 A

Fan Connector 4-Pin PWM

LED Connector

3-Pin Addressable RGB

Fan Life

80,000 hours

Compatible RGB
Software

Gigabyte RGB Fusion, MSI Mystic Light, ASUS AURA, ASRock Polychrome, Razer Chroma RGB

Warranty

2 years

Product Code

AK-FN112-WH

AKASA (@akasa_tech)



DISCOVER

About Akasa
Where to Buy
Press Room

SUPPORT



Legacy Products
Contact Us
Terms and Privacy

STAY UP TO DATE!

Subscribe now for free alerts on newly added products, exclusive deals and more.

name@example.com



 ENGLISH 

© AKASA ALL RIGHT RESERVED.