


DIGITUS VGA Monitor Extension Cable

AK-310203-100-E
EAN 4016032287124



VGA Monitor extension cable, HD15 M/F, 10.0m, 3Coax/7C, 2xferrite, be

For extension of monitor cables or devices (with HD15 plug), for example, PC, monitor or beamer / projector.

Offers high-quality protection against external interferences and prevents ghost images and other image faults.

- Support 1280 x 1024 pixel with 60Hz
- 3 x Coax for RGB and 7 x AWG28 signal wires
- 2 x ferrite filters
- Assortment: VGA Cables
- AWG: 28

- Cable type: 3Coax + 7-wire
- Connector 1: HD DSUB, 15-pin, plug
- Connector 2: HD DSUB, 15-pin, jack
- Connector surface: nickel-plated
- Display Data Channel: DDC2
- Ferrite filter: 2 x ferrite beads
- Hoods: molded
- Packaging: Polybag
- Wire material: CU
- Length: 10 m
- Shielding: Double shielding

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	15	15.30	40.00	33.00	24.00	31,680.00
Packaging Unit Inside	1	1.02	5.00	26.00	26.00	3,380.00
Packaging Unit Single	1	1.02	22.00	17.00	11.00	4,114.00
Net single without Packaging	1	1.01	22.00	17.00	11.00	4,114.00