




TOP VIEW




SIDE VIEW



ANGLED VIEW



Specifications			Notes	Revision History																
Description	Value	Unit		Version	Description	Date	Approved													
Directivity	Omnidirectional		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS 	1	Released from Engineering	10/21/2013	J.S													
Technology	Electret Condenser																			
Sensitivity	-44	(dB)																		
Frequency Range	40 ~ 20,000	(Hz)																		
Rated Voltage	2	(V)																		
Output Impedance	2,200	(Ohm)																		
Connection Method	Solder Pads																			
Voltage Range	1 ~ 10	(V)																		
Max Rated Current	0.45	(mA)																		
Minimum Signal to Noise Ratio	>60	(dB)																		
Operating Temperature	-40 ~ +85	°C																		
Storage Temperature	-40 ~ +85	°C																		
				Electret Condenser Microphone	MO064402-3															
				<table border="1"> <thead> <tr> <th>Drawn by</th> <th>Date</th> <th>Checked by</th> <th>Date</th> <th>Approved by</th> <th>Date</th> </tr> </thead> <tbody> <tr> <td>A.B.</td> <td>10/21/2013</td> <td>C.E.</td> <td>10/21/2013</td> <td>J.S</td> <td>10/21/2013</td> </tr> </tbody> </table>	Drawn by	Date	Checked by	Date	Approved by	Date	A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013				
Drawn by	Date	Checked by	Date	Approved by	Date															
A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[MO064402-3](#)