


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	90 (400.3)	EXTRA HEAVY	1.3 (590)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	90 (400.3)	EXTRA HEAVY	2.5 (1134)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	90 (400.3)	EXTRA HEAVY	2.8 (1270)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	90 (400.3)	EXTRA HEAVY	3.8 (1724)

NOTES:

*1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

W10001BH/06-SS-15129

CAD FILENAME/LAYERS
DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

								PANDUIT CORP. TINLEY PARK, ILLINOIS					
								PAN-TY RELEASABLE LASHING TIES - POLYPROPYLENE					
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) \pm .1(2.5)(.XXX) \pm .010(.25) (.XX) \pm .02(.5) ANGLES \pm -----					
								UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.					
---	---	---		CHANGED NOTE 1 "SEE CURRENT PRICE SHEET...", TO "SEE www.panduit.com ..."				---	---	DRAWN BY DWR		MAT'L: POLYPROPYLENE	
6	9/26/08	JABO		CORRECTED 'F' METRIC CONVERSION OF PRT5EH, WAS (510), NOW (511)				SS-15129	6	DATE 7-15-77		SCALE NONE	
REV	DATE	BY	CHK	DESCRIPTION				ECN	R	CUST	SUP	DRAWING NO. SS-15129	
												DWG A SIZE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PRT5EH-C100](#)