



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Multi-directional head
Product compatibility	XCKL XCKM XCKS

Associated body	ZCKM7H7 ZCKS1H29 ZCKM8H7 ZCKMD31 ZCKSD37 ZCKS5 ZCKS9 ZCKMD31H7 ZCKS6 ZCKL6H7 ZCKSD35H29 ZCKSD39H29 ZCKMD37 ZCKM6H7 ZCKSD37H29 ZCKSD31H29 ZCKMD39H7 ZCKS1 ZCKMD39H29 ZCKM7 ZCKSD35 ZCKM7H29 ZCKLD39 ZCKS2 ZCKS7H29 ZCKLD31 ZCKL1H7 ZCKM5H29 ZCKM9H29 ZCKMD39 ZCKM1 ZCKL5 ZCKM5 ZCKMD35 ZCKM1H29 ZCKLD35 ZCKL1 ZCKS5H29 ZCKMD31H29 ZCKM5H7 ZCKSD31 ZCKLD39H7 ZCKLD37 ZCKM6 ZCKL6 ZCKSD39 ZCKM8 ZCKS9H29 ZCKL8H7 ZCKS8H29 ZCKMD35H29 ZCKM1H7 ZCKL7 ZCKMD37H29 ZCKLD37H7 ZCKLD35H7 ZCKL8 ZCKMD37H7 ZCKL5H7 ZCKL7H7 ZCKS7 ZCKS8 ZCKMD35H7 ZCKM9 ZCKS6H29 ZCKS2H29 ZCKLD31H7 ZCKM6H29 ZCKM8H29
Movement of operating head	Multi-directional Rotary
Type of operator	Spring rod spring return
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Metal

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416 - LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	00785901646785
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1 lb(US) (0.05 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Package 1 Height	0.320 dm
Package 1 width	0.650 dm
Package 1 Length	2.220 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------