


order number: J01008A0824

BNC to N m-f



Technical Attributes	
Type	BNC (m)/N (f)
Remarks	-
Max. Frequency	4 GHz
Return Loss	29dB/1GHz; 28dB/2GHz; 22dB/4GHz
MIL-Std.	UG-349 A/U
Life	min. 500