

## Detailed Specifications

<b>Frame Width:</b>	119[mm]
<b>Frame Height:</b>	119[mm]
<b>Frame Depth:</b>	38[mm]
<b>Nominal Voltage:</b>	115[V]
<b>Frequency:</b>	60[Hz]
<b>Max. Air Flow:</b>	103.6[CFM]
<b>Max. Air Flow:</b>	2.9[m3 per min]
<b>Max. Static Pressure:</b>	0.31[In H2O]
<b>Max. Static Pressure:</b>	76.4[Pa]
<b>Fan Speed:</b>	2900[RPM]
<b>Noise:</b>	41[dB]
<b>Life Expectancy:</b>	25deg.C 100,000 hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Ingress Protection:</b>	none
<b>Starting Voltage:</b>	65[V]
<b>Input Power (+10% - 20%):</b>	14.5[V]
<b>Current:</b>	0.21[A]
<b>Mass:</b>	550[g]

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[11938MB-A1N-EA-00](#)