


Deep groove ball bearings, single row, seal on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
15	42	13	11,9	5,4	0,228	-	12000	0,082	6302-2RSH *



Calculation factors

k_r 0,03
 f_0 12