


### Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
50	80	16	22,9	16	0,71	-	5000	0,26	6010-2RS1 *



**Calculation factors**

$k_r 0,025$

$f_0 15$