





Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/04	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATION:
Material:
 Insulator: PBT, rated UL-94V-0
 Contacts: Brass
Contact Plating:
 Gold Flash over Nickel underplate overall
Electrical:
 Operating Voltage: 250V AC max.
 Current rating: 3 Amps max.
 Contact resistance: 20 mohms max
 Insulation resistance: 5000 Mohms min
 Dielectric withstanding voltage: 1000 VAC / minute
Mechanical:
 Mating durability: 500 cycles max.
Temperature Rating:
 Operating temperature: -55° TO +105°
 Environmental:
 Lead free, RoHS compliant.

A = .100 [2.54] X No. of Positions / 2 + .300 [7.60]
 B = .100 [2.54] X No. of Positions / 2 + .200 [5.08]
 C = .100 [2.54] X No. of Spaces

ADAM TECH

909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

BOX HEADER, VERTICAL PCB MOUNT,
 2 ROW, .100 PITCH, GOLD FLASH PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]	
TOLERANCES: EXCEPT AS NOTED	
INCHES	HOLDS
X ± .10	ØXX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010
APPROVALS	DATE
DRAWN	SS
CHECKED	
APPROVED	

TITLE	BOX HEADER, VERTICAL PCB MOUNT, 2 ROW, .100 PITCH, GOLD FLASH PLATED	
SIZE	PART NO.	BHR-XX-VUA
REF:	SCALE:	NTS
REV.	SHEET 1 OF 1	