


KERN DE 150K20DL

Langjähriges Erfolgsmodell mit staub- und spritzwassergeschütztem Auswertegerät



Measuring system

| | |
|-------------------------------|--|
| Adjustment options: | External calibration |
| Linearity: | 60 g 150 g |
| Readout [d]: | 20 g 50 g |
| Recommended adjusting weight: | 150 kg (M1) |
| Reproducibility: | 20 g 50 g |
| Resolution: | 3 3.000 |
| Stabilisation time: | 2,500 s |
| Warm up time: | 10 min 10 min |
| Weighing range [Max]: | 60 kg 150 kg |
| Weighing system: | Strain gauge |
| Weighing units: | dwt kg lb mo oz oz t l (HK) t l (Tw) tol |

Display

| | |
|-----------------------|----------|
| Display digit height: | 2,500 cm |
|-----------------------|----------|

Counting

| | |
|--|-------|
| Counting resolution: | 3750 |
| Minimum piece weight at piece counting (Laboratory): | 40 g |
| Minimum piece weight at piece counting (Normal): | 400 g |

Functions

| | |
|--|-----|
| Counting function: | yes |
| Percentage determination: | yes |
| Vibration-free weighing (Animal weighing program): | yes |

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 80 % |
| Maximum operating temperature: | 35 °C |
| Minimum ambient temperature: | 5 °C |

Power supply

| | |
|----------------|------------------------|
| Charging time: | 10 h |
| Input voltage: | 220 V - 240 V AC 50 Hz |
| n/a: | CH EURO UK US |

| | |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

Power supply

| | |
|---------------------------------|-------------------------|
| Operating time: | 12 h |
| Operating time (Backlight off): | 30 h |
| Operating time (Backlight on): | 15 h |
| Rechargeable battery: | Rchrg. battery optional |

Service

Adjustment at the location of installation: 961-249

| | |
|--------------------|---------|
| DAkkS Certificate: | 963-129 |
|--------------------|---------|

Category

| | |
|----------------|----------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Platform scale |

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 620 x 600 x 190 mm |
| Gross weight: | 17,700 kg |
| Net weight: | 15,600 kg |
| Shipping method: | Parcel service |

Construction

| | |
|---------------------------------------|-------------------|
| Cable length of display device: | 1,500 m |
| Dimensions of display device (WxDxH): | 225 x 110 x 55 mm |
| Dimensions of weighing plate (WxDxH): | 522 x 403 x 83 mm |
| Material weighing plate: | stainless steel |
| Weighing surface (WxD): | 522 x 403 mm |