



REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	HP 22/06/05		



- NOTES:
- SPECIFICATIONS
    - Contact Resistance: 50mΩ max
    - Insulator Resistance: 100MΩ min.
    - Current Rating: 1.5A per pin max.
    - Rated Voltage: 30V DC
    - Dielectric withstanding voltage: AC 500V For 1 minute
    - Contact: Copper Alloy
    - Housing: Thermoplastic(UL 94V-0)

2. PRODUCT NUMBER CODE:



Tel: 86-574-63508787  
 Fax: 86-574-63510817  
 E-mail: sale@connfly.com  
<http://www.connfly.com>  
 Add: East Industry Zone KuangYan  
 Town Cixi Ningbo China  
 P.C: 315333

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	IEEE 1394 6PIN MALE SOLDER TYPE	
X.	±0.60	X.	±5°	UNITS	mm			
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1106	
.XX	±0.25	.XX	±2°					
DRAWING TYPE		CUSTOMER			晨翔电子有限公司 <b>CONNFLY CONNFLY ELECTRONIC CO. LTD</b>			
SCALE		1:1	SHEET 1 OF 1					
DRAWING NO.		C-DS1106-XXX						