

## Acces. Special Cable Clamp EMC M25



Part number	19 62 000 5092
Specification	Acces. Special Cable Clamp EMC M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19620005092">https://b2b.harting.com/19620005092</a>

### Identification

Category	Accessories
Type of accessory	Cable gland
Description of the accessory	EMC version

### Technical characteristics

Wrench size	28
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	M25
Clamping range	9 ... 13 mm
Shielding diameter	4.8 ... 8 mm
Width across corners	31.2 mm

### Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Lead
	Nickel
	Naphthalene

## Commercial data

Packaging size	10
Net weight	55 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)