



FTTH Termination Box 2 x LCD/APC with Installation Cable

Technical Features

Fiber to the home termination box, fully assembled

Box 80 x 80 mm with 2x LCD/APC adapter

With 4-core breakout cable

Prefabricated on one side with pigtail 4x LC/APC



Flame retardant and halogen-free, B2ca-s1a, d0, a1

Compliant with EN 50575:2014+A1:2016

Art No.	Length	EAN Code
FB4LC20	20 m	4052792071665
FB4LC30	30 m	4052792071672
FB4LC40	40 m	4052792071689
FB4LC50	50 m	4052792071696
FB4LC60	60 m	4052792071702



Technical Drawings



Colored Coating Fiber: 250µm±1.5µm

Inner Jacket

Polyester yarn

Outer Jacket: White 2.2mm±0.2mm

Test:


TYPE	Single-Mode
Insertion Loss	≤0.3dB (IEC 61300-3-4)
Return Loss	APC ≥60dB (IEC 61300-3-6)
Test Wavelength	1310nm

www.2direct.de



Made in China

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



Package Content

1x FTTH Termination Box

Packaging Information

Art. No.	Packing Dimension	Packing Weight	Carton Q'ty	Packing Dimension	Packing Weight
FB4LC20	250 x 235 x 50 mm	0.336 kg	10 pcs	480 x 265 x 260 mm	3.86 kg
FB4LC30	250 x 235 x 50 mm	0.386 kg	10 pcs	480 x 265 x 260 mm	4.36 kg
FB4LC40	250 x 235 x 50 mm	0.432 kg	10 pcs	480 x 265 x 260 mm	4.82 kg
FB4LC50	250 x 235 x 50 mm	0.528 kg	10 pcs	480 x 265 x 260 mm	5.78 kg
FB4LC60	250 x 235 x 50 mm	0.48 kg	10 pcs	480 x 265 x 260 mm	5.3 kg