

Data sheet

3113.0 H 50,0/25



Wire-end ferrules, Max. wire cross-section: 50 mm², Length: 22 mm, Colour: natural

Business data

Article number	3113.0
Article name	H 50,0/25
GTIN (EAN)	4044211058180
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	2.2 g
Weight per piece (including packaging)	2.23 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules
Colour	Natural

Technical data

Dimensions

Length	22 mm
Diameter of copper pipe	10.3 mm
Diameter of feed-in funnel	13 mm
Wall thickness of copper pipe	0.3 mm

Connection data

Wire cross-section, max.	50 mm ²
Wire cross-section AWG, max.	1
Stripping length	22 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2024-01-23
REACH Candidate Substance Note	No
RoHS Conform	yes

Approvals

Standards and regulations

DIN 46228-1:1992

yes

Data sheet

3113.0 H 50,0/25



Media

Accessories
