



NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
3. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
4. JACK SCREWS: STEEL; NICKEL PLATED
5. CONNECTOR IS PART MARKED: 165X16949X CONEC ABC

| | | | | | | |
|--|-------------------------|-------------|------------|---------------------|---|--|
| THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND | tolerance ISO 2768-m | | dim. in mm | | scale: 2:1 (5:1) | |
| | | | | | material: SEE NOTES | |
| | | | | | title: | |
| | | | | | SCREEN CAP 50pos. for socket connector with jack screw | |
| | | | | | dwg no: 16K1A3574 DIN-A3 sh: 1 | |
| | | | | part no: 165X16949X | | |
| RoHS compliant | | | | | | |
| rev. | a | description | Original | date | | |
| name | | | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[165X16949X](#)