

TECHNICAL PARAMETERS/ 技术参数:

CATALOG NO. 目录编号	CURRENT RATING 额定电流	SAFETY APPROVALS 安全认证				REFERENCE (A ² ·Sec.) (RoHS) I ² T 参考值
		UR		cUR		
		L1	L2	L1	L2	
06T-010L	1A	●		●		0.061
06T-012L	1.2A	●		●		0.100
06T-013L	1.25A	●		●		0.106
06T-015L	1.5A	●		●		0.145
06T-016L	1.6A	●		●		0.156
06T-020L	2A	●		●		0.265
06T-025L	2.5A	●		●		0.453
06T-030L	3A	●		●		0.952
06T-032L	3.15A	●		●		0.990
06T-035L	3.5A	●		●		1.16
06T-040L	4A	●		●		1.38
06T-050L	5A	●		●		2.53

● DENOTES FOR APPROVED ● 表示已取得安全认证
L1 DENOTES FOR 32V L1 代表 32V
L2 DENOTES FOR 63V L2 代表 63V


ELECTRICAL CHARACTERISTICS/ 电气特性:

% of CURRENT RATING 额定电流的 %	BLOWING TIME 熔断时间	
100%	4 hours Min.	最快 4 小时
200%	1 second Min. 120 seconds Max.	最快 1 秒 最慢 120 秒
300%	0.05 seconds Min. 3 seconds Max.	最快 0.05 秒 最慢 3 秒
800%	0.0005 seconds Min. 0.05 seconds Max.	最快 0.0005 秒 最慢 0.05 秒


PACKING/ 包装:

5,000 PIECES TAPED AND REELED IN ONE BOX
每卷 5,000 只保险丝, 装入一个包装盒

BOX SIZE/ 包装盒尺寸:



Unit 单位: mm



0603, RoHS Compliant & Pb-Free
SURFACE MOUNT CHIP FUSE (SLOW-BLOW)
表面贴装片式保险丝 (慢断型)


INTERRUPTING CAPACITY / 分断能力:

50A 32V AC (1A) 35A 32V AC (1.2A-5A)
50A 32V DC (1A) 35A 32V DC (1.2A-5A)


Dimensions/ 尺寸:

Unit 单位: mm

TOP VIEW/ 上面:



SIDE VIEW/ 侧面:



Standards/ 标准: UL 248-1, UL 248-14

Operating Temperature/ 工作温度: -55°C ~90°C

Storing Temperature/ 储存温度: -55°C ~85°C

Resistance to soldering heat/ 耐焊接热性: 260°C, 10s Max.

Solderability/ 可焊性: 235°C ±5°C, 3.5s+0.5/-0s

06T AVERAGE I-T CHARACTERISTICS CURVE

(FOR REFERENCE ONLY) 06T 平均 I-T 曲线图 (仅供参考)

