



# silencer

## U-1/2

Part number: 2310

★ Core product range

FESTO



## Data sheet

| Feature                            | Value   |
|------------------------------------|---|
| Assembly position                  | Any   |
| Operating pressure                 | 0 ... 10 bar  |
| Flow rate to atmosphere            | 10,600 l/min  |
| Operating medium                   | Compressed air in accordance with ISO8573-1:2010 [7:-:-]                    |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Sound pressure level               | 80 dB(A)  |
| Ambient temperature                | -10 ... 70 °C   |
| Product weight                     | 58 g  |
| Pneumatic connection               | G1/2  |
| Material of silencer insert        | PE  |
| Materials note                     | Free of copper and PTFE<br>Conforms to RoHS                                 |