

## Han CGM-M M50x1,5 D.32-38mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5086
Specification	Han CGM-M M50x1,5 D.32-38mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005086">https://b2b.harting.com/19000005086</a>

### Identification

Category	Accessories
Series of hoods/housings	Han® CGM-M
Type of accessory	Cable gland

### Technical characteristics

Tightening torque	≤24 Nm (depending on the cable and the seal insert used)
Wrench size	57
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M50
Clamping range	32 ... 38 mm
Width across corners	60 mm

### Material properties

Material (seal)	NBR
Material (cable glands)	Brass
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
California Proposition 65 substances	Nickel
California Proposition 65 substances	Naphthalene

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780

## Commercial data

Packaging size	1
Net weight	220.7 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)