

D-Sub Plastic cover, Grey, Top Entry, Long knurled jackscrews



**TECHNICAL SPECIFICATIONS**

Material: UL Recognised Plastic Material  
 Operating Temperature: -55°C to +110°C  
 Cable Entry: Top  
 Thumbscrews: UNC 4-40  
 Cable O.D:  
     9-way Up to 7,0mm  
     15-way Up to 10,0mm  
     25-way Up to 11,0mm  
     37-way Up to 13,8mm  
     50-way Up to 14,0mm  
 Colour: Light Grey



**Features:**

- Available in sizes 9-15-25-37-50
- Suitable for any common Sub-D connector
- Long Jackscrews
- Re-openable
- Available in two colours: Black & Light Grey
- Also available in Metalized Version



Size CCOV	A	B	C
9-way	31,0	16,0	40,2
15-way	39,6	17,4	38,0
25-way	55,0	16,5	44,5
37-way	69,0	24,0	52,5
50-way	69,5	19,5	44,5

**Ordering information:**

Size:	P/N - Kitted:	Product Code:
9-way	2360-0102-31	CCOV 9-SCL-LG
15-way	2360-0102-32	CCOV15-SCL-LG
25-way	2360-0102-33	CCOV25-SCL-LG
37-way	2360-0102-34	CCOV37-SCL-LG
50-way	2360-0102-35	CCOV50-SCL-LG