

# Contact insert module - HC-1/2M-UT-F-6-PE - 1424438

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact insert module, Socket, Screw connection, 0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>, application: PE transmission, for housing size HC-EVO-M1



## Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626372570

## Technical data

### Dimensions

Height	43.7 mm
Width	30.6 mm
Length	7.7 mm

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

### Mechanical characteristics

Conductor cross section	0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Connection cross section AWG	20 ... 10
Contact diameter	4 mm
Insertion/withdrawal cycles	≥ 500

### General

Note	For HEAVYCON housing type HC-EVO-M1
	Connectors may be operated only when there is no load/voltage.
Series	HC-EVO-M1
Color	silver
Connection method	Screw connection

# Contact insert module - HC-1/2M-UT-F-6-PE - 1424438

## Technical data

### General

Contact type	turned
Flammability rating according to UL 94	V0

### Material data

Contact carrier material	Die-cast zinc alloy
--------------------------	---------------------

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Drawings

Dimensional drawing



## Classifications

eCl@ss

eCl@ss 10.0.1	27440217
eCl@ss 9.0	27440217

# Contact insert module - HC-1/2M-UT-F-6-PE - 1424438

## Classifications

### ETIM

ETIM 6.0	EC000438
ETIM 7.0	EC000438

## Approvals

### Approvals

---

### Approvals

EAC

---

### Ex Approvals

---

### Approval details

EAC		RU C- DE.BL08.B.00511
-----	--	--------------------------

## Accessories

### Accessories

#### Housing with locking latch

Housing - HC-EVO-M1-BWS-PLRBK - 1424437



Panel mounting base M1, with single locking latch, material: PA, height: 24 mm, cable gland: none, support sleeve: no, protective cover: no, Standard, for modular contact inserts

### Screwdriver tools

Philips screwdriver - SF-PH 1-80 - 1212559



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 1 x 80, 2-component grip, with non-slip grip

## Contact insert module - HC-1/2M-UT-F-6-PE - 1424438

### Accessories

Screwdriver - SF-SL 0,6X3,5-100 - 1212549



Screwdriver, bladed (lasered), size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

### Additional products

Contact insert module - HC-1/2M-UT-M-6-PE - 1424439



Contact insert module, Pin, leading, Screw connection, 0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>, application: PE transmission, for housing size HC-EVO-M1

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1424438](#)