



300V 8A 28-16AWG 1.5mm²
 Poles: 2-24P
 Pitch: 3.5mm (.138"), 3.81mm (.150")
Materials
 Housing: PA66 (UL 94V-0)
 Clamp: Phosphor Bronze, Nickel Plated
 Wire Cage: Brass, Nickel Plated
 Screw: M2, Steel (A3), Zinc Plated

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance
----------------	---------------	---------------	----------------	---------------------------



新莱亚电子科技

XILAINVA ELECTRONIC CO., LTD

图名/Title	文件编号/File No.	X. ° ±2°
XV2500FG-3.5		.X ° ±1°
XV2500FC-3.81	页序/Sheet	.XX ±0.05
		.XXX ±0.01

序号/Rev.No.

更改记录/Revision note

签名/Signature

日期/Date

备注/Remark

单位/Units: mm