

UNION CE Range

CE3F

Fixed Size 3 Rack and Pinion Door Closer



ASSA ABLOY

Application:


Introducing the new CE3F fixed size 3 rack and pinion door closer, [Click here to view video.](#)

Specification:

- Fixed size 3 rack and pinion door closer
- Maximum door width 950mm EN size 3
- 130° maximum angle of opening (controlled closing)
- Adjustable closing speed from 130° open to 15° open
- Adjustable latch action for final 15°
- Adjustable arm set for regular, transom and parallel arm installation
- Additional bracket included for parallel arm mounting

Finish:

- Silver finish, which allows it to blend in with any application where other traditional door closers are installed.



EN 1154 Size	Max Leaf Width	Max Leaf weight
1	750mm	20kg
2	850mm	40kg
3	950mm	60kg
4	1100mm	80kg
5	1250mm	100kg
6	1400mm	120kg

Standards:


- CE Marked to EN 1154 in all 3 mounting positions

3	8	3	1	1	3
---	---	---	---	---	---

- Fire rated for timber (FD120) and metal (FD240) fire doors
- Certifire approved



Technical Design:




UNION CE Range

CE3F

Fixed Size 3 Rack and Pinion Door Closer



ASSA ABLOY



Variants:

Code	Description
J-CE3F-SIL	UNION CE Marked Fixed Size 3 R&P Closer SIL