


quick coupling plug NPHS-S6-M-G14F

Part number: 8059262

★ Core product range

FESTO



Data sheet

| Feature | Value |
|---|--|
| Nominal size | 7.85 mm |
| Operating pressure complete temperature range | -0.95 ... 10 bar |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance classification CRC | 1 - Low corrosion stress |
| Ambient temperature | -10 ... 60 °C |
| Product weight | 28 g |
| Pneumatic connection, port 1 | Female thread 1/4 |
| Materials note | Conforms to RoHS |