

113A.4T | 113A.T - PHOSPHATED ADJUSTABLE WRENCHES




Norm :


NF ISO 6787, ISO 6787, DIN 3117, ASME B107.100


Description :

- Good access to the button = easy setting.
- Non-protruding moving jaw at maximum capacity.
- Pre-adjustment of jaw opening thanks to millimetric gradation.
- Left-hand button rotation.
- Range from 4" to 24".
- Presentation: phosphated body and "fine ground" head faces.



Informations :

	113A.4T
A [mm]	13
B [mm]	34
C x C1 [mm]	11,0 x 14,0
E [mm]	4,5
E1 [mm]	9,5
E2 [mm]	5,0
E3 [mm]	6,5
E4 [mm]	5,0

	113A.4T
L [mm]	114
L1 [mm]	13
[kg]	0.065