


Quantity per Pack: 10 pcs
8x31



Rated Current	Part Number Without Indicator	Part Number With Indicator	Watts Loss (W)	Voltage (AC)	Breaking Capacity (kA)
0.5	C08G0.5	C08G0.5I	2.60	400V	20 kA
1	C08G1	C08G1I	2.50		
2	C08G2	C08G2I	0.70		
4	C08G4	C08G4I	0.85		
6	C08G6	C08G6I	0.95		
8	C08G8	C08G8I	1.55		
10	C08G10	C08G10I	1.65		
12	C08G12	C08G12I	2.00		
16	C08G16	C08G16I	2.30		
20	C08G20	C08G20I	2.55		
25	C08G25	C08G25I	2.65		

10x38


Rated Current	Part Number Without Indicator	Part Number With Indicator	Watts Loss (W)	Voltage (AC)	Breaking Capacity (kA)
0.5	C10G0.5	C10G0.5I	1.43	500V	120 kA
1	C10G1	C10G1I	2.77		
2	C10G2	C10G2I	0.60		
4	C10G4	C10G4I	0.70		
6	C10G6	C10G6I	0.85		
8	C10G8	C10G8I	0.75		
10	C10G10	C10G10I	1.00		
12	C10G12	C10G12I	1.30		
16	C10G16	C10G16I	1.60		
20	C10G20	C10G20I	2.00		
25	C10G25	C10G25I	2.60	400V	
32	C10G32	C10G32I	2.90		

14x51


Rated Current	Part Number Without Indicator	Part Number With Indicator	Watts Loss (W)	Voltage (AC)	Breaking Capacity (kA)	
1	C14G1	C14G1I	3.90	690V	80 kA	
2	C14G2	C14G2I	0.90			
4	C14G4	C14G4I	1.00			
6	C14G6	C14G6I	1.15			
8	C14G8	C14G8I	1.00			
10	C14G10	C14G10I	1.30			
12	C14G12	C14G12I	1.70			
16	C14G16	C14G16I	2.00			
20	C14G20	C14G20I	2.50			
25	C14G25	C14G25I	3.30			
32	C14G32	C14G32I	3.50	500V	120 kA	
40	C14G40	C14G40I	4.85	400V		
50	C14G50	C14G50I	4.90			

22x58


Rated Current	Part Number Without Indicator	Part Number With Indicator	Watts Loss (W)	Voltage (AC)	Breaking Capacity (kA)
2	C22G2	C22G2I	1.00	690V	80 kA
4	C22G4	C22G4I	1.10		
6	C22G6	C22G6I	1.30		
8	C22G8	C22G8I	1.10		
10	C22G10	C22G10I	1.50		
12	C22G12	C22G12I	1.80		
16	C22G16	C22G16I	2.10		
20	C22G20	C22G20I	2.70		
25	C22G25	C22G25I	3.60		
32	C22G32	C22G32I	3.70		
40	C22G40	C22G40I	4.50		
50	C22G50	C22G50I	5.20		
63	C22G63	C22G63I	6.90	500V	120 kA
80	C22G80	C22G80I	7.80		
100	C22G100	C22G100I	8.60	400V	
125	C22G125	C22G125I	11.40		