

**NEW**

## Hose tail coupler



### Technical characteristics

**Technology:** "One push" safety system (avoids hose whip)

**Operating pressure:** 2 to 12 bar


**Flow rate at 6 bar:** 3530 l/min ( $\Delta P = 0,6$  bar)

**ID Passage:** 10,4 mm

**Temperature:** -15°C to +70°C

**Construction:** Polyamide composite body

**Highlight:** Anti-static, Excellent efficiency, Non scratch

	For hose ID (mm)	Parts Numbers
	9	ESI 111809EB
	10	ESI 111810EB
	13	ESI 111813EB
	16	ESI 111816EB
	19	ESI 111819EB