

[Custom Capabilities](#)[Test Accessories](#)[Plugs, Jacks, Posts](#)[Connectors](#)[Hardware](#)[S](#)[Home](#)[About Abbatron](#)[Products](#)[Locate Distributor  
or Representative](#)[Contact Us](#)[Request Information](#)[Site Map](#)

## Ceramic Spacers

- Ceramic spacers are Grade L-5 Steatite, glazed and fired at high temperature
- Threaded from each end as indicated in table
- Continuous safe operating Temperature Rating of 930°C(1700°F)
- Other size Options are available from factory in quantity, as are spacers with sizes at each end for adaption applications

 Ceramic Spacers drawing[Inventory Search](#)[Cross Reference](#)[UPS Tracking](#)

632 Arch Street, POB 726  
Meadville, PA 16335 USA  
814-724-6440  
Contact Webmaster  
© 2006

PART NO.	LENGTH	O.D.	THREAD		MIL NUMBER		
			SIZE	DEPTH			
2640	1/4	1/4	6-32	THRU	NL 523 W01 004		
2642	3/8	3/8		5/32			
2641	1/2	1/4		3/16			
2643		3/8		5/32			
2600		1/2		9/64			
2644	5/8	3/8		8-32		1/4	NL 523 W01 005
2607		1/2		3/16		NL 523 W02 005	
2602	3/4	3/8	6-32	1/4	NL 523 W01 006		
2645		1/2	8-32		NL 523 W02 006		
2608		3/8	6-32		NL 523 W01 008		
2603	1	1/2	8-32	3/8	NL 523 W02 008		
2646		3/4	10-32		NL 523 W03 008		
2609	1-1/4	3/8	6-32	3/8	NL 523 W01 010		
2615		1/2	8-32		NL 523 W02 010		
2604		3/4	10-32		NL 523 W03 010		
2610		1	1/4-20		7/16	NL 523 W04 010	
2616	1-1/2	1/2	6-32	3/8	NL 523 W01 012		
2647		3/8	8-32		NL 523 W02 012		
2605		1/2	10-32		NL 523 W03 012		
2611		1	1/4-20		1/2	NL 523 W04 012	
2617	2	3/8	6-32	3/8	NL 523 W01 016		
2623		1/2	8-32		NL 523 W02 016		
2606		3/4	10-32		NL 523 W03 016		
2612		1	1/4-20		5/8	NL 523 W04 016	
2618	2-1/2	1/2	6-32	3/8	NL 523 W01 020		
2648		3/4	10-32		NL 523 W03 020		
2613		1	1/4-20		3/4	NL 523 W04 020	
2619		5/8	3/8		NL 523 W02 024		
2649	3	1/2	8-32	3/8	NL 523 W03 024		
2625		3/4	10-32		NL 523 W04 024		
2614		1	1/4-20		5/8	NL 523 W04 024	
2620	4	3/4	10-32	3/8	NL 523 W03 032		
2626		1	1/4-20		3/4	NL 523 W04 032	
2650	5	1	1/4-20	5/8	NL 523 W04 040		
2621					NL 523 W04 040		
2627					NL 523 W04 048		
2628	6	1	1/4-20	5/8	NL 523 W04 040		
2629					NL 523 W04 048		

Maximum Thread Depth					
Thread Size	2 - 56	4 - 40	6 - 32	8 - 32	10 - 32
Thread Length Tapped Thru	0.375	0.500	1.000	1.000	1.000
Thread Length Tap each end	0.250	0.375	0.375	0.375	0.375

home | about abbatron | products | locate distributor or representative | contact us | request information | site map