

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	21.5[CFM]
Max. Air Flow:	0.61[m3 per min]
Max. Static Pressure:	0.2[In H2O]
Max. Static Pressure:	51.9[Pa]
Fan Speed:	4550[RPM]
Noise:	33.5[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.09[A]
Input Power:	2.2[W]
Mass:	65[g]
Tach / Locked Rotor Output:	No
Status:	EOL

DC Axial Fans