

# Product data sheet

Specifications



## Easy PDU, Metered, 1U, 16A, 230V, (8)C13

EPDU1016M

### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	Horizontal mounting brackets Installation guide User manual Cable
--------------------	--

### Physical

Cable length	2.50 m
--------------	--------

Colour	Black
--------	-------

Depth	4.4 cm
-------	--------

Height	4.44 cm
--------	---------

Net weight	0.7 kg
------------	--------

Width	48.2 cm
-------	---------

### Input

Input current limits	16 A
----------------------	------

Load capacity	3680 VA
---------------	---------

Network frequency	50/60 Hz
-------------------	----------

Plug standard	IEC 60320 C20
---------------	---------------

Input voltage	200 V 208 V 230 V
---------------	-------------------------

### Output

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

### Conformance

Product certifications	CE TÜV
------------------------	-----------

### Environmental

Ambient air temperature for operation	-5...45 °C
---------------------------------------	------------

Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

## Packing Units

Package 1 Weight	1.4 kg
Package 1 Height	8 cm
Package 1 width	56 cm
Package 1 Length	15 cm

## Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------