






## PLIO

**Material:** tinned copper  
**Insulation:** polypropylene  
**Temperature of use:** +105°C maxi (120°C short time)  
**Dimensions:** according to DIN 46228T4




### • PLIO bootlace insulated ferrules



type	article number	section mm <sup>2</sup>	insulator colours	a	L	dimensions (mm)			 *
						d1	d2	d4	
PLIO - 0,5	0649 0005 000	0,5	white	8	13,5	1,1	1,4	2,5	1000
PLIO - 0,75	0649 0010 000	0,75	blue	8	14	1,3	1,6	2,8	1000
PLIO - 1	0649 0015 000	1	red	8	14,5	1,5	1,8	3	1000
PLIO - 1,5	0649 0020 000	1,5	black	8	14,5	1,8	2,1	3,4	1000
PLIO - 2,5	0649 0030 000	2,5	grey	8	15	2,3	2,6	4,2	1000
PLIO - 4	0649 0040 000	4	orange	10	18	2,9	3,3	4,8	1000
PLIO - 6	0649 0050 000	6	green	12	20	3,6	4	6,2	500
PLIO - 10	0649 0060 000	10	brown	12	21	4,6	5	7,5	500
PLIO - 16	0649 0070 000	16	white	12	23	6	6,4	8,8	500
PLIO - 25	0649 0080 000	25	black	16	29	7,5	7,9	11	50
PLIO - 35	0649 0090 000	35	red	16	30	8,5	8,9	12,5	50
PLIO - 50	0649 0100 000	50	blue	20	36	10,5	11,1	15	50



\* string bags

### • PLIO bootlace ferrules for two conductors especially for bridges or looping-in of two conductors on the same contactor

type	article number	section mm <sup>2</sup>	insulator colours	a	L	dimensions (mm)				
						d1	d2	d4	d5	
PLIO - 2 x 0,5	0649 0210 000	2 x 0,5	white	8	15	1,5	1,8	4,5	2,3	1000
PLIO - 2 x 0,75	0649 0220 000	2 x 0,75	grey	8	15	1,8	2,1	5,1	2,6	1000
PLIO - 2 x 1	0649 0230 000	2 x 1	red	8	15	2,05	2,35	5,1	3	1000
PLIO - 2 x 1,5	0649 0240 000	2 x 1,5	black	8	16	2,3	2,6	6,4	3,5	1000
PLIO - 2 x 2,5	0649 0250 000	2 x 2,5	blue	10	18,5	2,9	3,3	7,5	4	1000
PLIO - 2 x 4	0649 0260 000	2 x 4	grey	12	23	3,8	4,2	8,6	4,9	1000
PLIO - 2 x 6	0649 0270 000	2 x 6	yellow	14	25	4,6	5	9,6	5,8	500
PLIO - 2 x 10	0649 0280 000	2 x 10	red	14	26	6,5	6,9	12,6	7	500



 B7/5






**BOX1 - BOX2**

**Specifications:** stacking (with central hole of 7 mm)  
rotating lid with window.

**Applications:** round dispenser box. Ideal for work on site.

A wide range of permanently available connectors  
No loss of time.




type	art. no.	Ø mm	height mm	weight g	
<b>BOX1 - 180012</b>	0649 0810 000	90	40	90	1
contents:	section (mm <sup>2</sup> )	quantity			
	0,5	50			
	0,75	100			
	1	100			
	1,5	100			
	2,5	50			
<b>BOX2 - 180022</b>	0649 0820 000	90	40	85	1
contents:	section (mm <sup>2</sup> )	quantity			
	4	50			
	6	20			
	10	20			
	16	10			






## Bootlace ferrules

**Material:** tinned electrolytic copper  
**Material insulation:** polypropylene  
**Operating temperature:** +105°C maxi (120°C short time)  
**Dimensions:** according to DIN 46228T4



type for section (mm <sup>2</sup> )	article number	colour	in reels of	a	L	dimensions (mm)			
						d1	d2	d4	
<b>Bandoliered bootlace ferrules in bags</b>									
WH 0,5 mm <sup>2</sup>	0649 0105 001	white	10 x 50 ferrules	8	14,5	1,1	1,4	2,6	500
BU 0,75 mm <sup>2</sup>	0649 0110 002	blue	10 x 50 ferrules	8	14,5	1,3	1,6	2,8	500
RD 1 mm <sup>2</sup>	0649 0115 007	red	10 x 50 ferrules	8	14,5	1,5	1,8	3	500
BK 1,5 mm <sup>2</sup>	0649 0120 010	black	10 x 50 ferrules	8	14,5	1,8	2,1	3,4	500
GY 2,5 mm <sup>2</sup>	0649 0130 013	grey	10 x 50 ferrules	8	14,5	2,3	2,6	4,2	500
<b>Bandoliered bootlace ferrules in dispenser boxes</b>									
YE 0,25K mm <sup>2</sup>	0649 0301 004	white	1000 ferrules	8	14,5	0,8	1,3	2	1000
TQ 0,35K mm <sup>2</sup>	0649 0303 086	turquoise	1000 ferrules	8	14,5	0,8	1,3	2	1000
WH 0,5K mm <sup>2</sup>	0649 0305 001	yellow	1000 ferrules	8	14,5	1,1	1,4	2,6	1000
BU 0,75K mm <sup>2</sup>	0649 0310 002	blue	1000 ferrules	8	14,5	1,3	1,6	2,8	1000
RD 1K mm <sup>2</sup>	0649 0315 007	red	1000 ferrules	8	14,5	1,5	1,8	3	1000
BK 1,5K mm <sup>2</sup>	0649 0320 010	black	1000 ferrules	8	14,5	1,8	2,1	3,4	1000
GY 2,5K mm <sup>2</sup>	0649 0330 013	grey	500 ferrules	8	14,5	2,3	2,6	4,2	500
<b>Bandoliered bootlace ferrules on reels</b>									
WH 0,5D mm <sup>2</sup>	0649 0306 001	white	3000 ferrules	8	14,5	1,1	1,4	2,6	3000
BU 0,75D mm <sup>2</sup>	0649 0311 002	blue	3000 ferrules	8	14,5	1,3	1,6	2,8	3000
RD 1D mm <sup>2</sup>	0649 0316 007	red	3000 ferrules	8	14,5	1,5	1,8	3	3000
BK 1,5D mm <sup>2</sup>	0649 0321 010	black	2500 ferrules	8	14,5	1,8	2,1	3,4	2500
GY 2,5D mm <sup>2</sup>	0649 0331 013	grey	1500 ferrules	8	14,5	2,3	2,6	4,2	1500



bandoliered bootlace ferrules in dispenser boxes



bandoliered bootlace ferrules on reels



crimping machine MC 25 for bandoliered bootlace ferrules  
Please contact our technical department.

