

WR 2

2-Channel Power Unit, 200 W (300 W)
Product no.: T0053377699N



Benefits

- > 2 independent channels with automatic tool recognition
- > Simultaneous operation up to 2 tools

For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning




Pre-heating plates



Technical Data

Dimensions L x W x H (mm)	280 x 240 x 103
Dimensions L x W x H (inches)	11,02 x 9,45 x 4,06
Weight (approx.) in kg	5.6
Voltage	230 V
Power	250 W (300 W)
Channels	2
Temperature range (depends on tool) °C	50 - 550
Temperature range (depends on tool) °F	150 - 999
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding socket	Via a 3.5 mm jack bush (initial state-hard-grounded)
Display	LCD
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	18
Vacuum	0,7 bar

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE