



## SM 150 x 18 Tpi - 5 pcs

### METAL: THIN KERF BLADES

- Improved tooth geometry for best speed and double the lifetime.
- Bi-metal quality cutting teeth with 8% cobalt giving the ultimate in performance and lifetime.
- TOUGH NECK™: Stamped indentations around the reception strengthens the blade at its weakest point.
- Slim 0.90 mm thick blade body optimised for maximum speed and flexibility.



Article Number	48005184
Blade length (mm)	150
Flush cut	No
Material type	Bi-Met,Co
Max. cutting capacity aluminium (mm)	-
Max. cutting capacity in steel plate (mm)	1,5 - 4
Max. cutting capacity inox (mm)	1,5 - 4
Max. cutting capacity metal pipe Ø (mm)	10 - 100
Max. cutting capacity non-ferrous metals (mm)	1,5 - 4