



ITEM	PAPT NAME	QTY	MATERIAL	FINISHING
③	Shell	1	Stainless Steel	
②	Terminal	5	Copper Alloy	
①	Housing	1	HI-TEMP.PLASIC UL 94V-0	BLACK

- 1.Contact Resistance:30mOHM Max.;
- 2.Dielectric Withstanding Voltage:100V AC For 1 Minute;
- 3.Insulation Resistance:1000M OHM Min.;
- 4.Mating And Unmating Force:  
Mating Force:35N Max/Unmating Force:8N Min;
- 5.Durability:10000 Cycles;

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: MICRO USB
ΔX					ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.:
ΔX					L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm	DWG NO.:
ΔX					4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	U-E-M5SS-Y-5
					16 < L ≤ 63 ±0.4				WEIGHT 1.0g
					L > 63 ±0.5				SHEET 1/1
									REVISION A0