

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301110112](#)
Status: **Active**
Overview: [Stringlights](#)
Description: LED String Light, 2 Light Engines, 12/3 SJTW Cable, 28W, NEMA 5-15 Plug and Receptacle, 7.62m (25.0') Overall Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

Agency Certification

UL E112216

General

Product Family Portable Lighting
 Series [130111](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating Wet Location
 Outlet Feed-Through
 Overview [Stringlights](#)
 Product Name LED String Light
 Type String Lights
 UPC 78172561011

Physical

Cord Length - Primary 4.27m (14.0')
 Cord Length - Secondary 0.305m (1.0')
 Depth 86.25mm (3.400")
 Duty Outdoor Use
 Guard Included No
 Guard Type N/A
 Height 121.92mm (4.800")
 Length 7.62m (25.0')
 Material - Globe Translucent Polycarbonate
 Mounting Style Stringer
 Packaging Type Carton
 Socket Construction N/A

Electrical


Bulb Type LED - 5000K
 Cord Type - Primary 12/3 SJTW
 Cord Type - Secondary 12/3 SJTW
 Lamp Type Integral LED
 Lamp Wattage - Maximum 14W
 Lumens 4256
 On/Off Switch No
 Voltage (Fixture) - Maximum 125V

Material Info

Engineering Number 123JQ25-14W10515M

Reference - Drawing Numbers

Sales Drawing 1301110100-000, 1301110100_INSTRUC-0



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130111 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[130111-0112](#)