



Led Color	Part No	VR	IF	Recommended Operating	IF	
					Nom	Max
White	TM-005-D-01	DC5V	20mA	20mA	3.0V	3.6V
Red	TM-005-D-02	DC5V	20mA	20mA	1.7V	2.4V
Blue	TM-005-D-03	DC5V	20mA	20mA	3.0V	3.6V
Green	TM-005-D-04	DC5V	20mA	20mA	1.9V	2.4V
Yellow	TM-005-D-05	DC5V	20mA	20mA	1.9V	2.4V

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑦	LED		1			
⑥	Hat		1	ABS		
⑤	Terminal	—	4	Brass (0.30t)	ag Plated	
④	Contact	—	1	F.ag/SUS		
③	Base	—	1	PA66		
②	Cover	—	1	PET		
①	Keystake	—	1	PA66		

DSND	DATE	SCALE: N/A	MODEL TYPE: LED SWITCH
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm	DWG NO.: TM-005-D
APPD	DATE	SIZE: A4	WEIGHT: 1.0g
XKB INDUSTRIAL PRECISION CO.,LIMITED			SHEET: 1/1
			REVISION: A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
△X					L ≤ 4	±0.2
△X					4 < L ≤ 16	±0.3
△X					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5

UNSPECIFIED TOLERANCES