

INSTA contactor with 2 NC contacts Contact for 230 V AC, 400V 20A
Control 230 V AC



Model	
Product brand name	SETRON
Product designation	Insta contactors
Design of the product	2 NC contacts
Type of voltage / of the operating voltage	AC
Type of voltage / for actuation	AC
Protection class	
Protection class IP	IP20
Switching capacity	
Switching capacity active power / with filament lamp load	1 000 W
Dissipation	
Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.7 W
Electricity	
Current / at AC / rated value	20 A
Main circuit	

Operating voltage / rated value	
<ul style="list-style-type: none"> • minimum • maximum 	250 V
Operating current / rated value	20 A

Control current

Control supply voltage	
<ul style="list-style-type: none"> • rated value • rated value / maximum 	230 V
	230 V

Product details

Product component / Slide for manual operation	No
Product extension / can be installed / supplementary devices	Yes

Number

Number of NC contacts	2
Number of NO contacts	0

Mechanical Design

Height	90 mm
Width	18 mm
Depth	71 mm
Installation depth	64 mm
Number of width units	1
Net weight	143 g

Certificates

Reference code / acc. to DIN EN 61346-2	Q
---	---

General Product Approval	Declaration of Conformity	other
--------------------------	---------------------------	-------



[Miscellaneous](#)



[Environmental Confirmations](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT5802-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT5802-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5802-0

CAX-Online-Generator

<http://www.siemens.com/cax>

