



MATERIALS:

Body – Brass, Tarnish Resistant Plating, Center Contact – Gold Plated Beryllium Copper

Finish: Body, Lockwasher and Hex Nut – Tarnish Resistant

Center Contact – Gold Plated

Dielectric – PTFE

Marking: “Pomona 4159”

RATINGS:

Nominal Impedance: 50 Ohms

Leakage Rate: Less than 10^{-7} cc/sec of tracer gas at one atmosphere.

ORDERING INFORMATION: Model 4159

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4159](#)