

## **KOBICONN**

## **Terminals** 159-3250, 159-7250







Dimensions: In.

SPECIFICATIONS				
Maximum Electric Rating:	105°C 300 volts			
Terminal Material:	Brass			
Thickness:	.017 (0.45mm)			
Insulation Material:	Nylon			

Mouser	Wire Range		Nema Tab	L	Insulated
Stock No.	AWG	mm <sup>2</sup>	(ln.)	(ln.)	Color
159-3250	22-16	1.25	.032x250	.913	Red
159-7250	16-14	2	.032x250	.866	Blue

Date Last Revised: 6/21/12

Available from Mouser Electronics 1-800-346-6873

www.mouser.com

Terminals

159-3250, 159-7250

KC-300024

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn: <u>159-3250</u> <u>159-7250</u>